ÖIUGO®

QN-PFW-BC GL/GLW222-302

Carriage for the QINEO GL/GLW222-302 TIG welding power source

If you use the QINEO for manual welding at different locations, the stable mounting carriage with large wheel diameters and a mounted holder for a shielding gas cylinder is ideal. Cooling module and inverter power unit are picked up and can be moved safely and easily over long distances and uneven floors. If the type of application of the QINEO changes, it can be quickly and easily switched to a platform that corresponds to the type of application.

- Stable mounting platform for moving the QINEO on uneven floors
- Tilt-proof mounting of a shielding gas cylinder with deep bottom for an easy change





ÖIUGO®

QN-PFW-BC GL/GLW222-302

Technical Data


Application

Process

- TIG DC
- TIG AC/DC

Questions about the product?

Your contact partner: Daniel Weber Tel.: +49 (0)2773 85-430 gt-sales@cloos.de



Technical modifications reserved Version: 19.05.2024

